

CONNECT\_

COMMUNICATE\_

CONTROL\_

## KONICA MINOLTA COLOR LASER PRINTER LINE



**magicolor® 2530DL**



**magicolor 2550EN/2550DN**



**magicolor 4650EN/4650DN**

<b>Printing Technology</b>	Color Laser	Color Laser	Color Laser
<b>Market</b>	Home office, Small business	Small business, Small to medium workgroups	Small business, Small to medium workgroups
<b>Maximum Speed</b>	5 ppm color, 20 ppm b&w	5 ppm color, 20 ppm b&w	25 ppm color, 25 ppm b&w
<b>Resolution</b>	2400 x 600 dpi	9600 x 600 dpi - class	9600 x 600 dpi - class
<b>Page Sizes</b>	Letter, A4, legal	Letter, A4, legal	Letter, A4, legal
<b>Standard RAM</b>	64 MB	128 MB DDR SDRAM (EN model) 256 MB DDR SDRAM (DN model)	256 MB
<b>Maximum RAM</b>	576 MB	640 MB DDR SDRAM	768 MB
<b>Internal Hard Disk</b>	N/A	Optional	Optional
<b>Processor</b>	TAK pro 800, 130 MHz	PowerPC, 300 MHz	Marvell Orion II, 500 MHz
<b>Media Types</b>	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 80 lb. cover stock	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 80 lb. cover stock	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 110 lb. index stock
<b>Standard Interfaces</b>	10/100BaseTX Ethernet, USB 2.0, USB 1.1 for Camera Direct Photo Print	10/100BaseTX Ethernet, USB 2.0, IEEE 1284 parallel, USB 1.1 (DN only)	10/100/1000BaseTX Ethernet, USB 2.0, IEEE 1284 parallel, USB 1.1 for Camera Direct Photo Print & Opt. USB Flash Drive Direct Print
<b>Compatibility</b>	Windows Vista/Server 2003/XP/2000/NT4/Me/98SE; Macintosh® OSX (10.2+); Linux® Red Hat 8.0+, SuSE 8.1+	PostScript® 3, PCL® 6, PDF 1.4*	PostScript 3, PCL 6; XPS*, PDF 1.6**, JPEG/TIFF** Direct Print
<b>Standard Paper Handling</b>	200-sheet multipurpose tray	200-sheet multipurpose tray; automatic duplexing (DN model)	250-sheet cassette, 100-sheet multipurpose tray, automatic duplexing (DN model)
<b>Optional Paper Handling</b>	500-sheet input feeder, automatic duplexing	500-sheet input feeder; automatic duplexing (EN model)	500-sheet lower feeder unit
<b>Monthly Duty Cycle</b>	35,000 pages	35,000 pages	90,000 pages
<b>MSRP***</b>	\$399	\$499 (EN model) \$699 (DN model)	\$699 (EN model) \$799 (DN model)



KONICA MINOLTA

CONNECT\_

COMMUNICATE\_

CONTROL\_

# KONICA MINOLTA COLOR LASER PRINTER LINE



magicolor 5550



magicolor 5570



magicolor 7450



magicolor 8650DN

<b>Printing Technology</b>	Color Laser	Color Laser	Color Laser	Color Laser
<b>Market</b>	High-volume, on-demand printing	High-volume, on-demand printing	General office & design	General office, design & publishing
<b>Maximum Speed</b>	27 ppm color, 31 ppm b&w	31 ppm color, 37 ppm b&w	24.5 ppm color, 24.5 ppm b&w	35 ppm color, 35 ppm b&w
<b>Resolution</b>	9600 x 600 dpi - class	9600 x 600 dpi - class	9600 x 600 dpi - class	19,200 x 600 dpi - class
<b>Page Sizes</b>	Letter, A4, legal, banner up to 8.5" x 47.24"	Letter, A4, legal, banner up to 8.5" x 47.24"	Letter, A4, legal, ledger, 12" x 18", banner up to 12.25" x 47.24"	Letter, A4, legal, ledger, 12" x 18", banner up to 12.25" x 47.24"
<b>Standard RAM</b>	256 MB DDR SDRAM	256 MB DDR SDRAM	256 MB DDR SDRAM	1024 MB DDR SDRAM
<b>Maximum RAM</b>	1024 MB DDR SDRAM	1024 MB DDR SDRAM	1024 MB DDR SDRAM	1024 MB DDR SDRAM
<b>Internal Hard Disk</b>	Optional	Optional	Optional	Optional
<b>Processor</b>	PowerPC MPC7448, 733 MHz	PowerPC MPC7448, 866 MHz	Power PC7447A, 733 MHz G4	PowerPC MC7447A, 1 GHz G4
<b>Media Types</b>	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 110 lb. index stock	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 110 lb. index stock	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 141 lb. index stock	Plain and laser paper, Transparencies, Envelopes, Laser-quality labels, Glossy stock, Up to 100 lb. cover stock
<b>Standard Interfaces</b>	10/100/1000BaseTX Ethernet, USB 2.0, IEEE 1284 parallel, USB 1.1 for Camera Direct Photo Print & USB Flash Drive Direct Print	10/100/1000BaseTX Ethernet, USB 2.0, IEEE 1284 parallel, USB 1.1 for Camera Direct Photo Print & USB Flash Drive Direct Print	10/100/1000BaseTX Ethernet, USB 2.0, IEEE 1284 parallel, USB 1.1 for Camera Direct Photo Print	10/100/1000BaseTX Ethernet, USB 2.0
<b>Compatibility</b>	PostScript 3, PCL 6; PDF 1.6**, XPS*, JPEG/TIFF** Direct Print	PostScript 3, PCL 6; PDF 1.6**, XPS*, JPEG/TIFF** Direct Print	PostScript 3, PCL 6; PDF 1.4*, JPEG/TIFF* Direct Print	PostScript 3, PCL 6; XPS*, PDF 1.6*, JPEG/TIFF* Direct Print
<b>Standard Paper Handling</b>	500-sheet cassette, 100-sheet multipurpose tray	500-sheet cassette, 100-sheet multipurpose tray	250-sheet multipurpose tray, 100-sheet manual feed tray	150-sheet multipurpose tray, 2 - 500-sheet cassettes, automatic duplexing
<b>Optional Paper Handling</b>	500-sheet input feeder (up to 2), automatic duplexing, 2-bin staple finisher, printer cabinet	500-sheet input feeder (up to 2), automatic duplexing, 2-bin staple finisher, printer cabinet	500-sheet cassette (up to 3), banner tray, automatic duplexing	500-sheet paper feed cabinet, 1,000-sheet paper feed cabinet, 2,500-sheet large-capacity paper feed cabinet, printer desk, banner tray, staple finisher (available with output tray, punch kit, saddle stitcher, 4-bin mailbin kit), floor finisher (available with punch kit)
<b>Monthly Duty Cycle</b>	120,000 pages	120,000 pages	120,000 pages	150,000 pages
<b>MSRP***</b>	\$999	\$1,199	\$2,999	STBD

Copyright © 2008 KONICA MINOLTA BUSINESS SOLUTIONS U.S.A., INC. KONICA MINOLTA and the KONICA MINOLTA logo are trademarks or registered trademarks of KONICA MINOLTA HOLDINGS, INC. magicolor is a registered trademark of KONICA MINOLTA BUSINESS SOLUTIONS U.S.A., INC. All other trademarks and registered trademarks are the property of their respective owners. Specifications and pricing are subject to change without notice.

\*Requires optional hard disk. \*\*Requires optional hard disk or compact flash card. \*\*\*Manufacturer's suggested retail price.

Item #: ColorCompare

04/08

CONNECT\_

COMMUNICATE\_

CONTROL\_



KONICA MINOLTA

## KONICA MINOLTA MONOCHROME LASER PRINTER LINE



pagepro 4650EN



pagepro 5650EN




PagePro 9100N

<b>Printing Technology</b>	Laser	Laser	Laser
<b>Market</b>	General business applications	Large workgroup printing	Large format for high-level business workgroup printing
<b>Speed</b>	35.7 ppm	45.6 ppm	35 ppm
<b>First-Page-Out Time</b>	8.7 seconds	7.9 seconds	10 seconds
<b>Maximum Resolution</b>	1200 x 1200 dpi	1200 x 1200 dpi	600 x 600 dpi, 1200 x 1200 dpi up to Legal — larger sizes with added RAM
<b>Page Sizes</b>	Letter, A4, legal, banner up to 8.5" x 35.4"	Letter, A4, legal, banner up to 8.5" x 35.4"	Letter, A4, legal, 11" x 17" edge-to-edge
<b>Standard RAM</b>	128 MB	128 MB	64 MB
<b>Maximum RAM</b>	384 MB	384 MB	512 MB
<b>Processor</b>	500 MHz	500 MHz	MIPS-RISC CPU, 250 MHz
<b>Internal Hard Disk</b>	Optional	Optional	Optional
<b>Standard Paper Input</b>	150-sheet multipurpose cassette, 550-sheet cassette	150-sheet multipurpose cassette, 550-sheet cassette	500-sheet cassette, 200-sheet multipurpose tray
<b>Paper Handling Options</b>	550-sheet lower cassette (up to 2), 500-sheet sorter/stacker, Automatic duplexer	550-sheet lower cassette (up to 2), 500-sheet sorter/stacker, Automatic duplexer	500-sheet lower feeder (up to 3) 4-bin mailbox Automatic duplexer
<b>Standard Interfaces</b>	Gigabit Ethernet® (10/100/1000BaseTX), IEEE 1284 parallel, USB 2.0, USB 1.1 Host Port	Gigabit Ethernet (10/100/1000BaseTX), IEEE 1284 parallel, USB 2.0, USB 1.1 Host Port	10/100BaseTX Ethernet, IEEE 1284 parallel, USB
<b>Optional Interfaces</b>	N/A	N/A	N/A
<b>Std. Printer Languages</b>	PostScript® 3, PCL® 6; XPS*, PDF 1.6**, JPEG/TIFF** Direct Print	PostScript 3, PCL 6; XPS*, PDF 1.6**, JPEG/TIFF** Direct Print	PostScript 3, HP-GL, PCL 6, Line printer, PDF
<b>Opt. Printer Languages</b>	N/A	N/A	ImageServer®, QUIC
<b>Monthly Duty Cycle</b>	150,000 pages	200,000 pages	150,000 pages
<b>MSRP***</b>	\$699	\$899	\$1,399

Copyright © 2007 KONICA MINOLTA BUSINESS SOLUTIONS U.S.A., INC. All rights reserved. KONICA MINOLTA and the KONICA MINOLTA logo are trademarks or registered trademarks of KONICA MINOLTA HOLDINGS, INC. PagePro is a trademark or registered trademark of KONICA MINOLTA BUSINESS TECHNOLOGIES, INC. ImageServer is a registered trademark of KONICA MINOLTA BUSINESS SOLUTIONS U.S.A., INC. All other trademarks and registered trademarks are the property of their respective owners. Specifications and pricing are subject to change without notice. \*Requires optional hard disk. \*\*Requires optional hard disk or compact flash card. \*\*\*Manufacturer's suggested retail price.

Item #: MonoCompare  
12/07

KONICA MINOLTA  
BUSINESS SOLUTIONS U.S.A., INC.  
100 Williams Drive  
Ramsey, NJ 07446  
[www.kmbs.konicaminolta.us](http://www.kmbs.konicaminolta.us)  
[www.kmbs.konicaminolta.us/solutions](http://www.kmbs.konicaminolta.us/solutions)



CONNECT\_

COMMUNICATE\_

CONTROL\_



KONICA MINOLTA

## KONICA MINOLTA LASER ALL-IN-ONE LINE



**magicolor® 2480MF**

Color Laser



**magicolor 2590MF**

Color Laser



**PagePro™ 1380 MF**

Monochrome Laser



**PagePro 1390 MF**

Monochrome Laser

	<b>Printing Technology</b>	<b>Market</b>	<b>Maximum Speed</b>	<b>Resolution</b>	<b>Page Sizes</b>
<b>PRINT</b>	Color Laser	Small & home offices, small to medium businesses	20 ppm b&w, 5 ppm color	2400 x 600 dpi	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	20 ppm b&w, 5 ppm color	2400 x 600 dpi	Letter, A4, legal
	Monochrome Laser	Small & home offices, small workgroups	21 ppm b&w	600 x 600 dpi	Letter, A4, legal
<b>COPY</b>	Monochrome Laser	Small & home offices, small workgroups	21 ppm b&w	1200 x 600 dpi	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	20 cpm b&w, 5 cpm color	2400 x 600 dpi	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	20 cpm b&w, 5 cpm color	600 x 600 dpi	Letter, A4, legal
<b>SCAN</b>	Color Laser	Small & home offices, small to medium businesses	20 cpm b&w, 5 cpm color	2400 x 600 dpi	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	20 cpm b&w, 5 cpm color	600 x 600 dpi	Letter, A4, legal
	Monochrome Laser	Small & home offices, small workgroups	20 cpm b&w	600 x 600 dpi	Letter, A4
	Monochrome Laser	Small & home offices, small workgroups	20 cpm b&w	600 x 600 dpi	Letter, A4, legal
	Monochrome Laser	Small & home offices, small workgroups	20 cpm b&w, 50 sec/pg color	12 sec/pg b&w, 50 sec/pg color	1200 x 1200 dpi
<b>FAX</b>	Monochrome Laser	Small & home offices, small workgroups	20 cpm b&w, 50 sec/pg color	12 sec/pg b&w, 50 sec/pg color	1200 x 1200 dpi
	Color Laser	Small & home offices, small to medium businesses	6 sec/pg b&w, 12 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
<b>Other Features</b>	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal
	Color Laser	Small & home offices, small to medium businesses	4 sec/pg b&w, 10 sec/pg color	24 bit	Letter, A4, legal

Copyright © 2007 KONICA MINOLTA BUSINESS SOLUTIONS U.S.A., INC. All rights reserved. KONICA MINOLTA and the KONICA MINOLTA logo are trademarks or registered trademarks of KONICA MINOLTA HOLDINGS, INC. PagePro is a trademark or registered trademark of KONICA MINOLTA BUSINESS TECHNOLOGIES, INC. magicolor is a registered trademark of KONICA MINOLTA BUSINESS SOLUTIONS, U.S.A., INC. All other trademarks and registered trademarks are the property of their respective owners. Specifications and pricing are subject to change without notice. \*Manufacturer's suggested retail price.